

TECHSPEC[®] 22mm CA, 35mm FL, Mounted MgF₂ Coated Plano-Convex Lens



Mounted MgF₂ Coated Plano-Convex (PCX) Lenses



Stock #12-996 CLEARANCE 10 TO 12 DAYS

- 1 +

₹5,390.00

ADD TO CART

Qty 1+

₹5,390.00

Volume Pricing

[Request Quote](#)

Get Product Downloads



Effective Focal Length EFL (mm):
35.00

Substrate: ☐
[N-BK7](#)

f/#:
1.4

Numerical Aperture NA: 0.36
Coating: MgF ₂ (400-700nm)
Type: Plano-Convex Lens
Wavelength Range (nm): 400 - 700
Back Focal Length BFL from Housing (mm): 30.42
Bevel: Protective bevel as needed
Clear Aperture CA (mm): 22.0
Coating Specification: R _{avg} ≤ 1.75% @ 400 - 700nm
Edge Thickness ET (mm): 2.00
Focal Length Specification Wavelength (nm): 587.6
Focal Length Tolerance (%): ±1
Radius R₁ (mm): 18.11
Surface Quality: 40-20
Lens Included: #45-146
Mount Included: #56-353
Mount Diameter (mm): 30.0
Extension Length (mm): 16.3
Total Length (mm): 20.3
Thread Type: C-Mount
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View