

SCHOTT RG-1000, 22mm CA, C-Mount Longpass Glass Color Filter



22mm CAC-Mount Longpass Glass Color Filter

Stock **#13-039** 10 TO 12 DAYS

- 1 + **₹8,091.00**

ADD TO CART

Qty 1-9
₹8,091.00
Qty 10+
₹7,221.00
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
25.40 ±0.38

Clear Aperture CA (mm):
22.0

Cut-Off Position λ_c (nm):
1000±6

Cut-On Wavelength (nm): 1,000.00
Density (g/cm³): 2.73
Glass/Filter Number: SCHOTT RG1000
Substrate: ☐ Colored Glass
Coating: Uncoated
Color: Black
Passband Limit 1 λ_{p1} (nm): 1300.00
Spectral Transmittance t_p (%): 90.00
Stopband Limit λ_s(nm): 730.00
Surface Quality: 80-50
Transformation Temperature (°C): 476.00
Type: Longpass Filter
Wavelength: IR
Reflection Factor P_d: 0.91
Substrate Thickness (mm): 3.00 ±0.2
Thread Type: C-Mount
Total Length (mm): 20.3
Mount Diameter (mm): 30.0
Filter Included: #32-760
Mount Included: #56-353

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View