

22mm Travel, Small Thick Base Single Movement



#03-682

Stock **#03-682** 20+ In Stock

-

1

+

₹12,983

ADD TO CART

Volume Pricing	
Qty 1-9	₹12,983 each
Qty 10+	₹11,465 each
Need More?	Request Quote

Product Downloads

General

English	Type:
Not Lockable	Note:

Physical & Mechanical Properties

Linear (X)	Type of Movement:
	Guide System:

Dovetail	
20 x 50	Stage Size (mm):
	Travel (mm):
22 (±11)	
Load Capacity (kg):	
3.5 Horizontal, 2.1 Vertical	
Straight Line Accuracy (µm):	
50	
Travel Per Knob Rotation (mm):	
15	
Weight (g):	
225	
Table Size (mm):	
20 x 35	

Hardware & Interface Connectivity

Type of Drive:	
Rack and Pinion	

Threading & Mounting

Mounting Threads:	
Stage: (1) ¼-20 Base: (3) ¼-20	

Regulatory Compliance

RoHS 2015:	
Exempt	
Certificate of Conformance:	
View	
Reach 233:	
Contains SVHC(s)	
Country of Origin:	
Japan	
Imported By:	
Edmund Optics India Private Limited	

Product Details

- Multiple Configurations Available
- High Load Capacity
- Ideal for Applications Requiring Long Travel
- Additional [Rack and Pinion Stages](#) Available

Basic Rack and Pinion Stages are ideal for applications requiring high load capacity or long travel. These stages feature horizontal load capacities of 3.5kg and vertical load capacities of 2.1kg. Each stage offers stage and base mounting holes and features steel construction with brass movement. Basic Rack and Pinion Stages are available in multiple configurations with varying stage sizes. These stages have a Dovetail guide system.

Technical Information

