

23" x 35", English Lab Table

See More by [TMC](#)



Stock **#54-255** **1 In Stock**

-

1

+

₹1,16,627

ADD TO CART

Volume Pricing	
Qty 1+	₹1,16,627 each
Need More?	Request Quote

Product Downloads

General	
English	Type:
Physical & Mechanical Properties	
50.00	Thickness (mm):
35.0	Length (inches):

23.0	Width (inches):
Construction: Stainless Steel (400 Series) Top and Bottom Plates, Plated Steel Honeycomb Core, High Pressure Laminate Core Sidewalls	
≤3	Core Cell Area (cm²):
0.13	Flatness (mm):
56.0	Weight (lbs):
430 Series Ferromagnetic Stainless Steel	Top Skin:
13.3 lb/ft³ (230 kg/m³)	Core Density:
< 0.5 in.² (3 cm²)	Core Cell Size:
275,000 PSI (19300 kg/cm²)	Core Shear Modulus:
0.075 in. (2 mm)	Top Skin Thickness:

Threading & Mounting

Mounting Threads: (693) ¼-20 Tapped on 1" Centerlines, on 1.5" Corners
--

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Country of Origin: United States
Imported By: Edmund Optics India Private Limited

Product Details

- Stainless Steel
- Economically Priced
- Lightweight Design

TMC™ CleanTop® Optical Honeycomb Breadboards are ultra-light (9 lbs/ft2, 44kg/m2) breadboards that employ countersunk, tapped holes in a thin top-skin of stainless steel. Top and bottom plates have a matte finish to lower reflectance and are ferromagnetic for mounting with magnetic bases. The tapped mounting holes allow for mounting with our English or Metric posts and post holders, as well as most commonly used optical mounts. TMC™ CleanTop® Optical Honeycomb Breadboards feature holes that are on 1" (25mm) centers with 1.5" (37.5mm) corners. Individually sealed holes allow for easy cleaning of spills

Note: Due to size and weight, shipping method and charges will differ from standard catalog charges; please contact our [Sales Department](#) for detailed information. Also note that these items will not be shipped overnight.