

232nm, 10nm FWHM, 50mm Dia. First Surface UV Bandpass Filter



UV Bandpass Filters

Stock #14-917 CLEARANCE 10 TO 12 DAYS

⊖ 1 ⊕

₹23,659.65

ADD TO CART

Qty 1+
₹23,659.65
Volume Pricing
Request Quote

Get Product Downloads

Diameter (mm): 50.00 +0.00/-0.25
Angle of Incidence (°): 0
Optical Density OD (Average): 4.0
Clear Aperture CA (mm): 45
Center Wavelength CWL (nm): 232.00 +3.0/-0

Full Width-Half Max FWHM (nm): 10.00 ±2
Substrate: Fused Silica (Corning 7980)
Minimum Transmission (%): 15
Coating: First Surface
Surface Quality: 80-50
Thickness (mm): 1.50 ±0.25
Type: Bandpass Filter
Blocking Wavelength Range (nm): 200 - 2000

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View