

2400 Grooves/mm, 12.7mm Square, UV Holographic Grating



Reflective Holographic Gratings

Stock **#43-776** 10 TO 12 DAYS

- 1 + **₹8,874.00**

ADD TO CART

Qty 1+
₹8,874.00
Volume Pricing
Request Quote

Get Product Downloads



Groove Density (grooves/mm):
2400

Wavelength Range (nm):
250 - 400

Dimensions (mm):
12.7 x 12.7 ±0.5

Coating:
Bare Aluminum

Construction: Holographic Grating
Length (mm): 12.70
Substrate:  Float Glass
Thickness (mm): 6.00 ±0.5
Type: Reflective Diffraction Grating
Wavelength: UV
Width (mm): 12.70
Alignment of Grooves to Edge (°): ±0.5
Absolute Peak Efficiency, Typical (%): 58
Peak Efficiency Avg, Typical (%): >43

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View
