

2400 Grooves/mm, 30mm Square, UV Holographic Grating



Reflective Holographic Gratings

Stock **#48-468** 10 TO 12 DAYS

- 1 + **₹19,575.00**

ADD TO CART

Qty 1+
₹19,575.00
Volume Pricing
Request Quote

Get Product Downloads



Groove Density (grooves/mm):
2400

Wavelength Range (nm):
250 - 400

Dimensions (mm):
30.0 x 30.0 ±0.5

Coating:
Bare Aluminum

Construction: Holographic Grating
Length (mm): 30.00
Substrate:  Float Glass
Thickness (mm): 9.50 ±0.5
Type: Reflective Diffraction Grating
Wavelength: UV
Width (mm): 30.00
Alignment of Grooves to Edge (°): ±0.5
Absolute Peak Efficiency, Typical (%): 58
Peak Efficiency Avg, Typical (%): >43

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View
