


## 2.5" Diameter, Uncoated Plastic Acrylic Window



Stock **#71-542** 16 In Stock

-

1

+

₹2,705

 Price inclusive of all taxes

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-5        | ₹2,705 each                   |
| Qty 6-25       | ₹2,164 each                   |
| Qty 26-49      | ₹2,034 each                   |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

| General                          |                         |
|----------------------------------|-------------------------|
| Protective Window                | Type:                   |
| Physical & Mechanical Properties |                         |
| 57.15                            | Clear Aperture CA (mm): |
| 2.50 ±0.010                      | Diameter (inches):      |

|                      |                     |
|----------------------|---------------------|
| 63.50 ±2.54          | Diameter (mm):      |
| 0.060 ±0.003         | Thickness (inches): |
| 1.52 ±0.08           | Thickness (mm):     |
| Protective as needed | Bevel:              |
| Smooth, Machined     | Edges:              |

Optical Properties

|            |                                        |
|------------|----------------------------------------|
| Uncoated   | Coating:                               |
| PMMA       | Substrate: <input type="checkbox"/>    |
| 1.49       | Index of Refraction (n <sub>d</sub> ): |
| 58         | Abbe Number (v <sub>d</sub> ):         |
| 400 - 1600 | Wavelength Range (nm):                 |

Material Properties

|    |                                                              |
|----|--------------------------------------------------------------|
| 60 | Coefficient of Thermal Expansion CTE (10 <sup>-6</sup> /°C): |
|----|--------------------------------------------------------------|

Regulatory Compliance

|                                                                                                                                                                                                         |                             |
|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------------|
| <a href="#">View</a>                                                                                                                                                                                    | Certificate of Conformance: |
| United States                                                                                                                                                                                           | Country of Origin:          |
| Edmund Optics India Private Limited<br>267, Greystone Building, Second Floor,<br>6th Cross Rd, Binnamangala,<br>Stage 1, Indiranagar, Bengaluru,<br>Karnataka, India 560038<br>Phone: +91- 80-6845 0000 | Imported By:                |

## Product Details

- Highly Scratch-Resistant
- High Visible Light Transmission
- Cost-Effective Alternative to Glass
- [Polycarbonate Plastic Windows](#) Also Available

Acrylic (PMMA) Plastic Windows are ideal for integration into lightweight optical systems. Compared to polycarbonate windows, acrylic windows are more scratch resistant and can be polished to restore optical quality but are more likely to chip or shatter. Acrylic (PMMA) Plastic Windows also provide a higher UV light transmission than polycarbonate and are recyclable. Acrylic windows are used in a wide variety of industrial and medical applications including aircraft windows, automobile headlights, and ophthalmological devices.

## Technical Information

