

## 25 x 25mm, 50R/50T, AR Coated Plate Beamsplitter



Stock #13-405 10 TO 12 DAYS

-

1

+

₹4,785.00

ADD TO CART

|                               |
|-------------------------------|
| Qty 1-9                       |
| ₹4,785.00                     |
| Qty 10+                       |
| ₹3,654.00                     |
| Volume Pricing                |
| <a href="#">Request Quote</a> |

Get Product Downloads



**Coating Specification:**  
Surface 1: Dielectric, ±5% R/T @ 550nm  
Surface 2: AR N/10 MgF2 @ 550nm

**Construction:**  
Plate

**Dimensional Tolerance (mm):**  
±0.38

|                                                           |
|-----------------------------------------------------------|
| <div>Dimensions (mm):<br/>25.00 x25.00</div>              |
| <div>Edges:<br/>Cut</div>                                 |
| <div>Reflection/Transmission Ratio (R/T):<br/>50/50</div> |
| <div>Substrate: <div></div><br/>Float Glass</div>         |
| <div>Surface Flatness (P-V):<br/>4 - 6λ</div>             |
| <div>Surface Quality:<br/>80-50</div>                     |
| <div>Thickness (mm):<br/>3.00</div>                       |
| <div>Type:<br/>AR Coated Beamsplitter</div>               |
| <div>Wavelength Range (nm):<br/>400 - 700</div>           |

## Regulatory Compliance

|                                                                 |
|-----------------------------------------------------------------|
| <div>RoHS 2015:<br/><a href="#">Compliant</a></div>             |
| <div>Certificate of Conformance:<br/><a href="#">View</a></div> |
| <div>Reach 235:<br/><a href="#">Compliant</a></div>             |