

SCHOTT KG5, 25mm Sq., 3mm Thick, Colored Glass Heat Absorbing Shortpass Filter

See More by [SCHOTT Optical Components](#)



Stock **#49-094** 10 TO 12 DAYS

-

1

+

₹3,480.00

ADD TO CART

Qty 1-10
₹3,480.00
Qty 11+
₹3,132.00
Volume Pricing
Request Quote

Get Product Downloads



Dimensions (mm):
25.0 x 25.0

Density (g/cm³):
2.53

Glass/Filter Number:
[SCHOTT KG5](#)

Substrate: Heat Absorbing Glass
Length (mm): 25.00
Operating Temperature (°C): 300 Maximum
Coating: Uncoated
Index of Refraction n_d: 1.51
Surface Quality: 60-40
Transformation Temperature (°C): 565
Thickness (mm): 3.00 ±0.38
Type: IR Cut-Off Filter
Width (mm): 25.00
Dimensional Tolerance (mm): ±0.25
Reflection Factor P_d: 0.92
Wavelength Range (nm): 300 - 2700
Bevel: Protective as needed

Regulatory Compliance

RoHS 2015: Compliant
Reach 223: Compliant
Certificate of Conformance: View