

254 x 313mm, 4-6λ Mirror



4-6λ First Surface Mirrors

Stock **#32-248** 10 TO 12 DAYS

⊖ 1 ⊕

₹13,311.00

ADD TO CART

Qty 1-5
₹13,311.00
Qty 6+
₹10,658.00
Volume Pricing
Request Quote

Get Product Downloads

Surface Flatness (P-V):
4 - 6λ

Substrate: ☐
Float Glass

Surface Quality:
80-50

Dimensions (mm):

254.0 x 313.0 ±0.76
Coating Specification: R _{avg} >85% @ 400 - 700nm
Coating: Protected Aluminum (400-700nm)
Coating Type: Metal
Angle of Incidence (°): 45.00
Bevel: Protective as needed
Clear Aperture (%): >90
Thickness (mm): 6.00
Type: Flat Mirror
Wavelength Range (nm): 400 - 700
Length (mm): 313.00
Width (mm): 254.00

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant