

SCHOTT AS87ECO, 25.4 x 50.8mm, 0.1mm Thick, Ultra-Thin Window

See More by [SCHOTT Optical Components](#)



Stock #12-314 10 TO 12 DAYS

- 1 + ₹3,132.00

ADD TO CART

Qty 1-10
₹3,132.00
Qty 11+
₹2,501.00
Volume Pricing
Request Quote

Get Product Downloads

Abbe Number (v_d):
59.5

Bevel:
Protective as needed

Clear Aperture (%):
90

Clear Aperture CA (mm):

22.86 x 45.72
Dimensions (mm): 25.40 x 50.80
Thickness (mm): 0.10 ±0.01
Coating: Uncoated
Coefficient of Thermal Expansion CTE (10⁻⁶/°C): 8.7
Density (g/cm³): 2.46
Index of Refraction n_d: 1.504
Knoop Hardness (kg/mm²): 500
Poisson's Ratio: 0.216
Substrate: AS 87 ECO
Surface Quality: 80-50
Type: Protective Window
Wavelength Range (nm): 200 - 3200
Young's Modulus (GPa): 73.3
Length (mm): 50.80
Width (mm): 25.40

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant