

TECHSPEC®

25.4 x 646mm EFL 15° Protected Aluminum 100Å Off-Axis Parabolic Mirror



Stock **#35-540** [CONTACT US](#)

[Other Coating Options](#)

-

1

+

₹21,315.00

ADD TO CART

Qty 1-5
₹21,315.00
Qty 6+
₹19,184.00
Volume Pricing
Request Quote

Get Product Downloads



Type:
Off-Axis Parabolic Mirror

Diameter (mm):
25.40 +0.00/-0.38

Effective Focal Length EFL (mm):
646.00

Focal Length Tolerance (%) : ±1
Radius of Curvature (mm) : 1,270.00
Coating : Protected Aluminum (400-2000nm)
Coating Type : Metal
Coating Specification : R _{avg} ≥85% @400 - 700nm R _{avg} ≥97% @2,000 - 12,000nm
Off-Set Angle (°) : 15
Parent Focal Length PFL (mm) : 635.00
Surface Figure, RMS : λ/4
Surface Roughness (Angstroms) : <100 RMS
Wavelength Range (nm) : 400 - 2000
Clear Aperture (%) : 90
Surface Quality : 80-50
Compatible Mounting Plates : #47-111
Substrate : Aluminum 6061-T6
Y Offset (mm) : 167.2
Reflected Wavefront, RMS : λ/2

Regulatory Compliance

RoHS 2015 : Compliant
Certificate of Conformance : View
Reach 235 : Compliant