

25.4mm Clear Aperture 33R/67T, Pellicle Beamsplitter



Pellicle Beamsplitters

Stock **#39-480** [CONTACT US](#)

- 1 + **₹18,879.00**

ADD TO CART

Qty 1-10
₹18,879.00
Qty 11+
₹16,052.00
Volume Pricing
Request Quote

Get Product Downloads



Clear Aperture CA (mm):
25.4

Coating:
Dielectric

Coating Specification:
33/67 @ 400 - 700nm

Construction: Pellicle
Diameter (mm): 34.90
Housing: Black Anodized Aluminum
Index of Refraction n_d: 1.5
Mount Thickness (mm): 4.76
Reflection/Transmission Ratio (R/T): 33/67 $\pm$ 5%
Substrate: ☐ Nitrocellulose
Surface Quality: 40-20
Type: Pellicle Beamsplitter
Wavelength Range (nm): 400 - 700
Mounting Threads: 2-56
Thickness (μm): 2 +0.3/-0.0

Regulatory Compliance

RoHS 2015: Compliant
REACH 201: Compliant
Certificate of Conformance: View