

TECHSPEC® 25.4mm Dia., 6.35mm Thick, 980nm, λ/10 N-BK7 Window



TECHSPEC λ/10 Laser Line Coated Windows

Stock **#39-699** CLEARANCE 10 TO 12 DAYS

- 1 +

₹6,086.00

ADD TO CART

Qty 1+

₹6,086.00

Volume Pricing

[Request Quote](#)

Get Product Downloads



Angle of Incidence (°):
0

Clear Aperture CA (mm):
22.86

Coating:
Laser V-Coat (980nm)

Design Wavelength DWL (nm):
980

Diameter (mm):

25.40 +0.00/-0.10
Substrate: N-BK7
Index of Refraction n_d: 1.516
Surface Quality: 10-5
Thickness (mm): 6.35 ±0.20
Type: Laser Line Window
Parallelism (arcmin): <3
Bevel: Protective as needed
Clear Aperture (%): 90
Abbe Number (v_d): 64.17
Coating Specification: R _{abs} <0.25% @ 980nm
Surface Flatness (P-V): λ/10
Damage Threshold, By Design: 15 J/cm² @ 980nm, 20ns, 20Hz
Edges: Fine Ground

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View