

25.4mm Dia f/2 Uncoated, Molded Acrylic Aspheric Lens



Molded Acrylic Aspheric Lenses



Stock **#48-171** 10 TO 12 DAYS



1



₹5,133.00

ADD TO CART

Qty 1-10	
₹5,133.00	
Qty 11+	
₹4,263.00	
Volume Pricing	
Request Quote	

Get Product Downloads

Diameter (mm):
25.40 ±0.1

Effective Focal Length EFL (mm):
50.80 @ 632.8nm

Numerical Aperture NA:

0.25
Back Focal Length BFL (mm): 46.2
Substrate: ☐ PMMA
Focal Length Tolerance (%): ±1
Aspheric Design Wavelength (nm): 632.8
Coating: Uncoated
Clear Aperture CA (mm): 23.9
Edge Thickness ET (mm): 4.00
Center Thickness CT (mm): 6.95
f##: 2.00
Bevel: Protective bevel as needed
Operating Temperature (°C): 80.00
Radius R (mm): 24.89
Type: Aspheric Lens
Wavelength Range (nm): 400 - 1100
Conjugate Distance: Infinite

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View