

[See all 37 Products in Family](#)

25.4mm Dia f/4 Uncoated, Molded Acrylic Aspheric Lens



Molded Acrylic Aspheric Lenses



Stock #48-172 **20+ In Stock**

₹4,437

ADD TO CART

Volume Pricing	
Qty 1-10	₹4,437 each
Qty 11-49	₹3,698 each
Need More?	Request Quote

Product Downloads

General

Aspheric Lens **Type:**

Physical & Mechanical Properties

25.40 ±0.1 **Diameter (mm):**

Clear Aperture CA (mm):

23.9

4.00 **Edge Thickness ET (mm):**

5.45 **Center Thickness CT (mm):**

Protective as needed **Bevel:**

49.78 **Radius R (mm):**

Optical Properties

102.00 @ 632.8nm **Effective Focal Length EFL (mm):**

0.12 **Numerical Aperture NA:**

98.00 **Back Focal Length BFL (mm):**

PMMA **Substrate:**

±1 **Focal Length Tolerance (%):**

632.8 **Aspheric Design Wavelength (nm):**

Uncoated **Coating:**

4.00 **f#:**

400 - 1100 **Wavelength Range (nm):**

Infinite **Conjugate Distance:**

Environmental & Durability Factors

80.00 **Operating Temperature (°C):**

Regulatory Compliance

[Compliant](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**

[Compliant](#) **Reach 242:**

United States **Country of Origin:**

Edmund Optics India Private Limited **Imported By:**

Product Details

- Prescription Information Available
- Reduced Spherical Aberration
- Broadband AR Coating Option

Our molded acrylic aspheres are economical solutions for a variety of photonic applications. With available prescription information, these lenses are easily integrated into both benchtop and OEM applications. They are available uncoated and with broadband antireflection coatings. Standard diameter sizes of 0.5" and 1" allow them to be easily mounted using our full line of [lens mounts](#).

Compatible Mounts