


TECHSPEC®

25.4mm Dia. NIR, Precision Broadband Laser Mirror



Stock #45-597 10 TO 12 DAYS

-

1

+

₹13,572.00

ADD TO CART

Qty 1-5
₹13,572.00
Qty 6+
₹11,919.00
Volume Pricing
Request Quote

Get Product Downloads



Surface Quality:
20-10

Type:
Laser Mirror

Clear Aperture (%):
>80

Durability:

ML-M-13508-C
Back Surface: Ground
Coating Specification: R _{avg} >99% @ 700 - 900nm
Wavelength Range (nm): 700 - 900
Surface Flatness (P-V): λ/10
Irregularity (P-V) @ 632.8nm: λ/20
Coating Type: Dielectric
Coating: Dielectric Mirror (700-900nm)
Diameter (mm): 25.40 +0.0/-0.2
Thickness (mm): 8.00 ±0.3
Angle of Incidence (°): 0-45
Substrate: ☐ BOROFLOAT®
Note: Optical Power: λ/10
Damage Threshold, By Design: ☐ 10 J/cm ² @ 10ns

Regulatory Compliance

RoHS 2015: Compliant
REACH 201: Compliant
Certificate of Conformance: View