

TECHSPEC[®] 25.4mm Dia., Uncoated, Ultrafast Thin Window



Stock #11-750 10 TO 12 DAYS

-

1

+

₹9,788.00

ADD TO CART

Qty 1-5
₹9,788.00
Qty 6+
₹8,809.00
Volume Pricing
Request Quote

Get Product Downloads



Coating:

Uncoated

Diameter (mm):

25.40 +0.00/-0.10

Substrate:

[Fused Silica](#) (Corning 7980)

Index of Refraction n_d :

1.458
Surface Quality: 20-10
Thickness (mm): 1.00 ±0.10
Type: Ultrafast Window
Bevel: Protective as needed
Clear Aperture (%): 90
Transmitted Wavefront, P-V: λ/6
Abbe Number (v _d): 67.8
Parallelism (arcsec): ≤30
Wavelength Range (nm): 200 - 2200
Fused Silica Grade: 7979 0G
Edges: Fine Ground
Type of Window: Glass

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View