

25.4mm Dia. x -100mm FL, Uncoated, ISP Optics Zinc Selenide (ZnSe) Negative Meniscus Lens | ZC-NM-25-100

See More by [ISP Optics](#)



Stock **#24-903**

10 TO 12 DAYS

-

1

+

₹41,325.00

ADD TO CART

Qty 1+
₹41,325.00

Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
25.40 +0.00/-0.13

Effective Focal Length EFL (mm):
-100.00 @ 10.6µm

Substrate:  Zinc Selenide (ZnSe), CVD Grade
f/#: 3.94
Numerical Aperture NA: 0.13
Coating: Uncoated
Type: Meniscus Lens
Wavelength Range (nm): 600 - 18000
Center Thickness CT (mm): 3.00 ±0.20
Centering (arcmin): <3
Clear Aperture (%): 90
Clear Aperture CA (mm): 22.86
Edge Thickness ET (mm): 3.60
Focal Length Tolerance (%): ±2
Model Number: ZC-NM-25-100
Radius R₁ (mm): 104.24
Radius R₂ (mm): 414
Surface Quality: 60-40
Irregularity (P-V) @ 10.6μm: λ/20

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View