

TECHSPEC[®] 25.4mm Dia. x 50mm FL, Uncoated, Laser Grade PCX Lens



TECHSPEC Laser Grade PCX Lenses

Stock **#38-625** 10 TO 12 DAYS

[Other Coating Options](#)

-

1

+

₹15,747.00

ADD TO CART

Qty 1-5

₹15,747.00

Qty 6+

₹12,528.00

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
25.40 +0.00/-0.025

Effective Focal Length EFL (mm):
50.00 @ 355nm

Back Focal Length BFL (mm):
45.71

Coating: Uncoated
Substrate: Fused Silica (Coming 7980)
Surface Quality: 10-5
Power (P-V) @ 632.8nm: λ
Irregularity (P-V) @ 632.8nm: $\lambda/10$
Focal Length Tolerance (%) : ± 1
Centering (arcmin): <1
Center Thickness CT (mm): 6.35 $\pm$ 0.10
Edge Thickness ET (mm): 2.35
Radius R₁ (mm): 23.80
Clear Aperture CA (mm): 21.59
f#: 1.97
Numerical Aperture NA: 0.25
Type: Plano-Convex Lens
Bevel: Protective Bevel As Needed
Wavelength Range (nm): 200 - 2200

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View