

TECHSPEC[®] 25.4mm Dia. Linear Plastic Polarizer (XP42-200)



Stock #85-919

10 TO 12 DAYS

-

1

+

₹2,262.00

ADD TO CART

Qty 1-5
₹2,262.00
Qty 6+
₹1,740.00
Volume Pricing
Request Quote

Get Product Downloads

Diameter (mm):
25.40 +0.0/-0.3

Extinction Ratio:
9000:1

Substrate:
[XP42-200 on PMMA](#)

Operating Temperature (°C):
-40 to +80

Thickness (mm): 2.22 ±0.25
Transmission (%): Single: 42 Parallel: 36 Crossed: <0.004
Type: Linear Polarizer
Construction: Polarizing Film on PMMA
Wavelength Range (nm): 400 - 700
Polarization Efficiency (%): >99.98

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant