

25.4mm Sq 20R/80T, UV-NIR Polka-Dot Beamsplitter



Stock #18-711 10 TO 12 DAYS

-

1

+

₹16,356.00

ADD TO CART

Qty 1-10
₹16,356.00
Qty 11+
₹13,903.00
Volume Pricing
Request Quote

Get Product Downloads



Angle of Incidence (°):
0 - 45

Center to Center Spacing (mm):
0.15

Clear Aperture (%):
90

Coating: Square Aluminum (AlMgF ₂) Apertures
Construction: Polka-Dot
Dimensional Tolerance (mm): +0.0/-0.5
Dimensions (mm): 25.4 x 25.4
Minimum Aperture (mm): 2.00
Operating Temperature (°C): 150 Maximum
Parallelism (arcmin): <3
Reflection/Transmission Ratio (R/T): 20/80
Reflection/Transmission Tolerance (%): ±5 @ 45°
Substrate:  Fused Silica (Corning 7980)
Surface Quality: 80-50
Thickness (mm): 1.65 ±0.1
Type: Standard Beamsplitter
Wavelength Range (nm): 250 - 2000

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View