

25° Diffusing Angle 2" x 2" Unmounted Sheet



Stock #65-887 CLEARANCE 10 TO 12 DAYS

- 1 +

₹21,098.00

ADD TO CART

Qty 1-5
₹21,098.00
Qty 6+
₹17,944.00
Volume Pricing
Request Quote

Get Product Downloads

Angle Tolerance (°): ±2.5
Diffusing Angle (°): 25 (FWHM)
Dimensional Tolerance (mm): ±0.5
Dimensions (inches): 2 x2

Dimensions (mm): 50.80 x 50.80
Operating Temperature (°C): -30 to +100 (Maximum of 240 Hours)
Substrate: ☐ Polycarbonate
Thickness (mm): 0.78
Transmission (%): >85
Type: Holographic Diffuser
Wavelength Range (nm): 400 - 700
Width (mm): 50.80
Construction: Unmounted
Damage Threshold, By Design: ☐ 0.22 J/cm ² @ 1064nm, 10ns (typical)
Length (mm): 50.80

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant