

TECHSPEC® 25mm Dia., 0.55mm Thick, Uncoated, Gorilla Glass® Window



Gorilla® Glass Windows



Stock #21-233 10 TO 12 DAYS



1



₹2,610.00

ADD TO CART

Qty 1-5

₹2,610.00

Qty 6+

₹2,001.00

Volume Pricing

[Request Quote](#)

Get Product Downloads



Bevel:
Protective as needed

Chemical Strengthening Cycle (hours):
8

Clear Aperture (%) : 90.00
Clear Aperture CA (mm) : 22.50
Diameter (mm) : 25.00 ±0.25
Thickness (mm) : 0.55 ±0.05
Coating : Uncoated
Coefficient of Thermal Expansion CTE (10⁻⁶/°C) : 7.58 (0 to +300°C)
Density (g/cm³) : 2.39
Edges : Fine Ground
Index of Refraction n_d : 1.5
Poisson's Ratio : 0.22
Substrate : Gorilla® Glass
Surface Quality : 80-50
Type : Protective Window
Wavelength Range (nm) : 350 - 2200
Young's Modulus (GPa) : 70

Regulatory Compliance

RoHS 2015 : Compliant
Certificate of Conformance : View
Reach 233 : Compliant