

TECHSPEC® 25mm Dia., 1mm Thick VIS 0° Coated, 1λ Fused Silica Window



Stock **#19-848** 10 TO 12 DAYS

-

1

+

₹8,048.00

ADD TO CART

Qty 1-5
₹8,048.00
Qty 6+
₹6,438.00
Volume Pricing
Request Quote

Get Product Downloads



Abbe Number (v_d):
67.8

Bevel:
Protective as needed

Clear Aperture (%):
90

Clear Aperture CA (mm):

22.50
Diameter (mm): 25.00 +0.00/-0.20
Thickness (mm): 1.00 ±0.38
Coating: VIS 0° (425-675nm)
Coating Specification: R _{avg} ≤0.4% @ 425 - 675nm
Coefficient of Thermal Expansion CTE (10⁻⁶/°C): 0.52 (+5 to +35°C) 0.57 (0 to +200°C) 0.48 (-100 to +200°C)
Density (g/cm³): 2.20
Edges: Fine Ground
Index of Refraction n_d: 1.458
Knoop Hardness (kg/mm²): 522
Parallelism (arcmin): <5
Poisson's Ratio: 0.16
Substrate: Fused Silica (Corning 7980)
Surface Quality: 60-40
Transmitted Wavefront, P-V: 1λ
Type: Protective Window
Wavelength Range (nm): 425 - 675
Young's Modulus (GPa): 73
Damage Threshold, Reference: ☐ 5 J/cm² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant