

TECHSPEC® 25mm Dia 405nm 45°, Laser Diode Mirror



Stock **#63-139** [CONTACT US](#)

- 1 + **₹9,918.00**

ADD TO CART

Qty 1+
₹9,918.00

Volume Pricing
Request Quote

Get Product Downloads



Surface Quality:
10-5

Type:
Laser Mirror

Parallelism (arcmin):
<3

Clear Aperture (%):
>90

Back Surface:
Ground

Reflection at DWL (%): 99.8
Coating Specification: R _{abs} >99.8% @ 405nm R _{avg} >98% @ 375 - 435nm
Wavelength Range (nm): 375 - 435
Surface Flatness (P-V): λ/10
Coating Type: Dielectric
Coating: Dielectric Mirror (375-435nm)
Design Wavelength DWL (nm): 405
Diameter (mm): 25.00 +0.0/-0.2
Thickness (mm): 6.00 ±0.2
Angle of Incidence (°): 45
Substrate: ☐ Fused Silica (Corning 7980)

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View