

TECHSPEC®

25mm Dia., Enhanced Aluminum,  $\lambda/10$  Stemmed Mirror



TECHSPEC® Stemmed Mirror



Stock #14-579 CLEARANCE 10 TO 12 DAYS

- 1 +

₹11,484.00

ADD TO CART

Qty 1-5

₹11,484.00

Qty 6+

₹9,135.00

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):  
25.00 +0.00/-0.10

Surface Flatness (P-V):  
 $\lambda/10$

|                                                                      |
|----------------------------------------------------------------------|
| <b>Substrate:</b> <a href="#">Fused Silica</a> (Corning 7980)        |
| <b>Back Surface:</b><br>Commercial Polish                            |
| <b>Surface Quality:</b><br>20-10                                     |
| <b>Coating Specification:</b><br>R <sub>avg</sub> >95% @ 450 - 650nm |
| <b>Coating:</b><br>Enhanced Aluminum (450-650nm)                     |
| <b>Coating Type:</b><br>Metal                                        |
| <b>Clear Aperture (%):</b><br>90.00                                  |
| <b>Edges:</b><br>Ground, protective bevel as needed                  |
| <b>Thickness (mm):</b><br>13.00 ±0.20                                |
| <b>Type:</b><br>Stemmed Mirror                                       |
| <b>Wavelength Range (nm):</b><br>450 - 650                           |
| <b>Compatible Kinematic Mount:</b><br><a href="#">#58-853</a>        |
| <b>Stem Diameter (mm):</b><br>12.50 +0.00/-0.10                      |
| <b>Stem Length (mm):</b><br>6.50 ±0.20                               |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS:</b><br><a href="#">Compliant</a>                  |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |