


TECHSPEC®

25mm Dia. High Transmission Linear Polarizing Film (XP44-40)



High Transmission Linear Polarizing Film (XP44-40)

Stock #19-024 CLEARANCE 10 TO 12 DAYS

- 1 +

₹2,170.65

ADD TO CART

Qty 1-10

₹2,170.65

Qty 11+

₹1,909.65

Volume Pricing

[Request Quote](#)

Get Product Downloads

Diameter (mm):
25.00 +0.0/-0.3

Extinction Ratio:
2000:1

Substrate: [Polymer Film XP44-40](#)

Operating Temperature (°C):

-40 to +80
Thickness (mm): 0.40 ±0.05
Transmission (%): Single: 44.2 ±1.5 Parallel: 38.6 Crossed: <0.02
Type: Linear Polarizer
Construction: Polarizing Film
Note: The polarisation axis is parallel to the notch on the polariser
Wavelength Range (nm): 400 - 700
Polarization Efficiency (%): >99.95

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Contains SVHC(s)