


TECHSPEC® 25mm Dia., Protected Gold, λ /10 Stemmed Mirror



TECHSPEC® Stemmed Mirror



Stock **#14-581** CLEARANCE CONTACT US

- 1 + **₹16,008.00**

ADD TO CART

Qty 1-5
₹16,008.00
Qty 6+
₹12,789.00
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
25.00 +0.00/-0.10

Surface Flatness (P-V):
 λ /10

Substrate: Fused Silica (Corning 7980)
Back Surface: Commercial Polish
Surface Quality: 20-10
Coating Specification: R _{avg} >96% @ 700 - 2000nm R _{avg} >96% @ 2000 - 10,000nm
Coating: Protected Gold (700-10000nm)
Coating Type: Metal
Clear Aperture (%) : 90.00
Edges: Ground, protective bevel as needed
Thickness (mm): 13.00 ±0.20
Type: Stemmed Mirror
Wavelength Range (nm): 700 - 10000
Compatible Kinematic Mount: #58-853
Stem Diameter (mm): 12.50 +0.00/-0.10
Stem Length (mm): 6.50 ±0.20

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View