


TECHSPEC® 25mm Dia Protected Silver, λ/20 Mirror



Stock #34-392 10 TO 12 DAYS

- 1 + **₹15,834.00**

ADD TO CART

Qty 1-5
₹15,834.00
Qty 6+
₹12,615.00
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
25.00 +0.00/-0.20

Surface Flatness (P-V):
λ/20 (flatness pre-coating)

Substrate: ▢
[Fused Silica](#) (Corning 7980)

Back Surface:

Commercial Polish
Surface Quality: 20-10
Coating Specification: R _{avg} >98% @ 450 - 2000nm R _{avg} >98% @ 2000 - 10,000nm
Coating: Protected Silver (450-10000nm)
Coating Type: Metal
Clear Aperture (%): 90.00
Edges: Ground, protective bevel as needed
Parallelism (arcsec): 30.00
Thickness (mm): 4.00 ±0.20
Type: Flat Mirror
Wavelength Range (nm): 450 - 10000

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant