

TECHSPEC® 25mm Dia x 125mm FL Uncoated, Illumination Grade PCX Cylinder Lens



Stock #47-744 10 TO 12 DAYS

⊖ 1 ⊕ **₹6,090**

ADD TO CART

Qty 1-5

₹6,090

Qty 6+

₹4,872

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
25.00

Effective Focal Length EFL (mm):
125.00

Substrate:
[N-BK7](#)

f/#:
5

Numerical Aperture NA:
0.1

Coating:
Uncoated

Type:
Cylinder Lens, Plano-Convex

Wavelength Range (nm):
350 - 2200

Back Focal Length BFL (mm):
123.02

Center Thickness CT (mm):
3.00

Center Thickness Tolerance (mm):
±0.1

Dimensional Tolerance (mm):
+0.0/-0.2

Edge Thickness ET (mm):
1.78

Focal Length Tolerance (%):
±3

Radius R₁ (mm):
64.60

Surface Quality:
60-40

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Reach 224:
[Compliant](#)

Certificate of Conformance:
[View](#)
