

TECHSPEC[®] 25mm Dia. x 25mm FL, 8-12μm Coated Germanium Meniscus Lens



Stock #87-967 10 TO 12 DAYS

-

1

+

₹45,153.00

ADD TO CART

Qty 1-5
₹45,153.00
Qty 6+
₹36,122.00
Volume Pricing
Request Quote

Get Product Downloads

Diameter (mm):
25.00 +0.0/-0.1

Effective Focal Length EFL (mm):
25.00

Substrate: ☐
Germanium (Ge)

f/#:
1.00

Numerical Aperture NA: 0.50
Coating: BBAR (8000-12000nm)
Type: Meniscus Lens
Wavelength Range (nm): 8000 - 12000
Back Focal Length BFL (mm): 23.34
Center Thickness CT (mm): 2.50
Center Thickness Tolerance (mm): ±0.10
Centering (arcmin): <3
Clear Aperture (%): 90.00
Coating Specification: R _{avg} <3.0% @ 8 - 12µm
Edge Thickness ET (mm): 1.3
Focal Length Specification Wavelength (µm): 10.6
Radius R₁ (mm): 28.32
Radius R₂ (mm): 42.46
Surface Quality: 60-40
Wavelength Range (µm): 8 - 12

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant