


TECHSPEC[®] 25mm Dia. x 38mm FL, MgF₂ Coated, Plano-Convex Lens



UV Fused Silica Plano-Convex (PCX) Lenses



Stock #18-064 CLEARANCE 10 TO 12 DAYS

- 1 +

₹12,833.00

ADD TO CART

Qty 1-5

₹12,833.00

Qty 6+

₹10,266.00

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
25.00 -0.025

Effective Focal Length EFL (mm):
38.00 @ 587.6nm

Back Focal Length BFL (mm): 33.03
Coating: MgF ₂ (400-700nm)
Coating Specification: R _{avg} ≤1.75% @ 400 - 700nm
Substrate: ☐ Fused Silica (Corning 7980)
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 3 Rings
Irregularity (P-V) @ 632.8nm: 0.5 Rings
Focal Length Tolerance (%): ±1
Centering (arcmin): <1
Center Thickness CT (mm): 7.25 ±0.10
Edge Thickness ET (mm): 1.96
Radius R₁ (mm): 17.42
Clear Aperture CA (mm): 24
f/#: 1.52
Numerical Aperture NA: 0.33
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 400 - 700
Damage Threshold, By Design: ☐ 10 J/cm ² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant