

TECHSPEC® 25mm Dia. x 40mm FL, 3 - 12μm Coated, Ge Plano-Convex Lens



Stock **#87-946** 10 TO 12 DAYS
[Other Coating Options](#)

- 1 + **₹41,325.00**

ADD TO CART

Qty 1-5
₹41,325.00
Qty 6+
₹33,060.00
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
25.00 +0.0/-0.1

Effective Focal Length EFL (mm):
40.00 @ 10.6μm

Back Focal Length BFL (mm):
39.25

Coating: BBAR (3000-12000nm)
Coating Specification: R _{avg} <5.0% @ 3 - 12μm
Substrate: ☐ Germanium (Ge)
Surface Quality: 60-40
Centering (arcmin): <3
Center Thickness CT (mm): 3.00 ±0.10
Edge Thickness ET (mm): 2.35
Radius R₁ (mm): 120.16
Clear Aperture CA (mm): 24
f/#: 1.6
Numerical Aperture NA: 0.31
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 3000 - 12000

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant