

[See all 22 Products in Family](#)

25mm Dia. x 50mm FL Protected Aluminum, Concave Mirror



Stock #43-466 **1 In Stock**

⊖ 1 ⊕ MRP ₹5,499

● Price inclusive of all taxes

ADD TO CART

| Volume Pricing | |
|----------------|-------------------------------|
| Qty 1-49 | ₹5,499 each |
| Qty 50-99 | ₹4,641 each |
| Need More? | Request Quote |

Product Downloads

General

Spherical Mirror **Type:**

Physical & Mechanical Properties

±0.5 **Thickness Tolerance (mm):**

25.00 ±0.50 **Diameter (mm):**

Clear Aperture (%):

90

Edge Thickness ET (mm):

3.0

Optical Properties

Metal **Coating Type:**

Protected Aluminum (400-2000nm) **Coating:**

400 - 2000 **Wavelength Range (nm):**

50.00 **Effective Focal Length EFL (mm):**

N-BK7 **Substrate:**

f/2 **Aperture (f#):**

Coating Specification:
R_{avg} >85% @400 - 700nm
R_{avg} >90% @400 - 2000nm

±2 **Focal Length Tolerance (%):**

100.00 **Radius R₁ (mm):**

80-50 **Surface Quality:**

100.00 **Radius of Curvature (mm):**

Regulatory Compliance

Compliant **RoHS 2015:**

View **Certificate of Conformance:**

Compliant **Reach 247:**

United States **Country of Origin:**

Imported By:
Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Product Details

- Ideal for Focusing Light
- Aluminum and Gold Coating Options
- Available in Sizes Ranging from 9 - 50mm

Concave Spherical Mirrors are ideal for collecting and focusing light in a wide range of applications. These mirrors are available with protected metallic coatings covering the UV, VIS, and IR spectrum. A protective layer increases the coating's durability and prevents corrosion. Concave Spherical Mirrors are available in diameters ranging from 9-50mm for ease of system integration.

Technical Information



