

TECHSPEC® 25mm Dia. x 75mm FL NIR II Coated Calcium Fluoride PCX Lens



TECHSPEC Calcium Fluoride Plano-Convex (PCX) Lenses

Stock #22-530 [CONTACT US](#)

⊖ 1 ⊕ MRP ₹25,424

● Price inclusive of all taxes

ADD TO CART

| Volume Pricing | |
|----------------|-------------------------------|
| Qty 1-5 | ₹25,424 each |
| Qty 6-25 | ₹20,380 each |
| Qty 26-49 | ₹19,169 each |
| Need More? | Request Quote |

Product Downloads

General

Plano-Convex Lens **Type:**

Physical & Mechanical Properties

25.00 +0.00/-0.10 **Diameter (mm):**

Centering (arcmin):

| | |
|----------------------------------|--------------------------------------|
| Center Thickness CT (mm): | 4.00 ±0.1 |
| Edge Thickness ET (mm): | 1.67 |
| Clear Aperture CA (mm): | 24 |
| Bevel: | Protective as needed |
| Optical Properties | |
| Effective Focal Length EFL (mm): | 75.00 @266nm |
| Back Focal Length BFL (mm): | 73.63 |
| Coating: | NIR II (750-1550nm) |
| Substrate: | Calcium Fluoride (CaF ₂) |
| Surface Quality: | 40-20 |
| Power (P-V) @ 632.8nm: | λ |
| Irregularity (P-V) @ 632.8nm: | λ/2 |
| Radius R ₁ (mm): | 34.66 |
| f#: | 3.00 |
| Numerical Aperture NA: | 0.17 |
| Wavelength Range (nm): | 200 - 7000 |
| Axis Orientation: | Random |


Regulatory Compliance

| | |
|-----------------------------|---|
| RoHS 2015: | Compliant |
| Certificate of Conformance: | View |
| Reach 235: | Compliant |
| Country of Origin: | Singapore |
| Imported By: | Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000 |

Product Details

- Low Index of Refraction
 - Vacuum Grade UV Substrate
 - Uncoated, MS-NIR, and NIR II Broadband AR Coating Options
- TECHSPEC® Calcium Fluoride Plano-Convex Lenses are ideal for demanding applications that require superior performance from the ultraviolet through the mid-wave infrared spectra. The lenses' low refractive index, high laser damage threshold, and low axial and radial-stress birefringence are highly suitable for use with Excimer lasers or for integration into infrared systems. Additionally, calcium fluoride features low solubility and offers superior hardness to comparable fluoride-based substrates, making these PCX lenses capable of withstanding harsh environments and exposure to the elements. TECHSPEC® Calcium Fluoride Plano-Convex Lenses are offered in 12.5mm, 25mm, and 50mm diameters. The lenses are available uncoated, MS-NIR, or with NIR II broadband AR coating options.
- Note:** Calcium fluoride is a relatively soft optical material and requires careful handling as it is very easily scratched. Calcium fluoride is also susceptible to thermal shock.

Technical Information



Special Handling

These optics require special handling to avoid damage and ensure long-term performance. Proper handling, cleaning, and storage are essential to maintain optical quality. Explore our [Optics Cleaning Resources](#) for step-by-step guides and best practices. For personalized assistance, [Email us](#) or [Chat](#) with our technical support team.



Component Handling Tools