

TECHSPEC® 25mm Dia x -12.5mm FL, Protected Aluminum, Convex Mirror



Convex Mirrors

Stock **#87-655** 10 TO 12 DAYS

- 1 + **₹4,133.00**

ADD TO CART

Qty 1-5
₹4,133.00
Qty 6+
₹3,306.00
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
25.00

Focal Length FL (mm):
-12.50

Center Thickness CT (mm):
5.00

Clear Aperture (%) : 90.00
Coating: Protected Aluminum (400-700nm)
Coating Specification: R _{avg} >85% @400 - 700nm
Coating Type: Metal
Dimensional Tolerance (mm): +0.0/-0.1
Edge Thickness ET (mm): 1.65
Focal Length Tolerance (%): ±2
Radius R (mm): 25.0
Substrate:  N-BK7
Surface Accuracy: λ/2
Surface Quality: 60-40
Thickness Tolerance (mm): ±0.1
Type: Spherical Mirror
Wavelength Range (nm): 400 - 700

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant