

TECHSPEC® 25mm Dia. x -25mm FL, VIS-NIR, Inked, Double-Concave Lens



Stock **#45-930-INK** 17 TO 22 D= DAYS

- 1 + **₹5,220.00**

ADD TO CART

Qty 1-9
₹5,220.00
Qty 10+
₹4,698.00
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
25.00

Effective Focal Length EFL (mm):
-25.00

Substrate: N-SF11
f/#: 1.00
Numerical Aperture NA: 0.50
Coating: VIS-NIR (400-1000nm)
Type: Double-Concave Lens
Wavelength Range (nm): 400 - 1000
Back Focal Length BFL (mm): -25.69
Bevel: Protective bevel as needed
Center Thickness CT (mm): 2.50
Center Thickness Tolerance (mm): ±0.10
Centering (arcmin): <1
Clear Aperture CA (mm): 24.00
Coating Specification: R _{abs} ≤0.25% @ 880nm R _{avg} ≤1.25% @ 400 - 870nm R _{avg} ≤1.25% @ 890 - 1000nm
Edge Thickness ET (mm): 6.33
Focal Length Tolerance (%): ±1
Radius R₁=R₂ (mm): -39.78
Surface Quality: 40-20

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View