

TECHSPEC<sup>®</sup> 25mm Dia x -50mm FL, Protected Aluminum, Convex Mirror



Convex Mirrors

Stock **#87-657** **6 In Stock**

-

1

+

₹3,854

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-5        | ₹3,854 each                   |
| Qty 6-25       | ₹3,075 each                   |
| Qty 26-49      | ₹2,919 each                   |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

| General                          |                           |
|----------------------------------|---------------------------|
| Spherical Mirror                 | Type:                     |
| Physical & Mechanical Properties |                           |
| 25.00                            | Diameter (mm):            |
| 3.00                             | Center Thickness CT (mm): |

|           |                             |
|-----------|-----------------------------|
| 90.00     | Clear Aperture (%):         |
| +0.0/-0.1 | Dimensional Tolerance (mm): |
| 2.22      | Edge Thickness ET (mm):     |
| 100.0     | Radius R (mm):              |
| ±0.1      | Thickness Tolerance (mm):   |

Optical Properties

|                                    |                                     |
|------------------------------------|-------------------------------------|
| -50.00                             | Focal Length FL (mm):               |
| Protected Aluminum (400-700nm)     | Coating:                            |
| R <sub>avg</sub> >85% @400 - 700nm | Coating Specification:              |
| Metal                              | Coating Type:                       |
| ±2                                 | Focal Length Tolerance (%):         |
| N-BK7                              | Substrate: <input type="checkbox"/> |
| λ/2                                | Surface Accuracy:                   |
| 60-40                              | Surface Quality:                    |
| 400 - 700                          | Wavelength Range (nm):              |

Regulatory Compliance

|                                     |                             |
|-------------------------------------|-----------------------------|
| Compliant                           | RoHS 2015:                  |
| View                                | Certificate of Conformance: |
| Compliant                           | Reach 247:                  |
| United States                       | Country of Origin:          |
| Edmund Optics India Private Limited | Imported By:                |

## Product Details

- Precision Polished Surface
  - λ/2 Surface Accuracy
  - Variety of Coating Options Offered
- TECHSPEC® Convex Mirrors are ideal for expanding an imaging system's field of view without introducing chromatic aberrations. TECHSPEC Convex Mirrors utilize a precision polished surface with a λ/2 surface accuracy to maintain image quality. These optical mirrors create virtual, upright images. Shorter focal lengths generate wider fields of view, while longer focal lengths minimize distortion.

## Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
  - High-precision surface quality and flatness
  - Tight tolerances and complex geometries
  - Scalable production—from prototype to volume
- Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).