

TECHSPEC® 25mm Diameter 30R/70T, VIS N/10 Plate Beamsplitter



TECHSPEC® N/10 Plate Beamsplitters

Stock **#34-412** 10 TO 12 DAYS

- 1 + **₹17,052.00**

ADD TO CART

Qty 1-5
₹17,052.00
Qty 6+
₹13,659.00
Volume Pricing
Request Quote

Get Product Downloads



Coating Specification:
Surface 1: 30/70 ±5% @ 550nm, ±10% @ 400 - 700nm
Surface 2: AR R_{avg} ≤1%, R_{abs} ≤2% @ 400 - 700nm

Construction:
Plate

Diameter (mm):

25.00
Dimensional Tolerance (mm): ±0.10
Edges: Protective Bevel as needed
Reflection/Transmission Ratio (R/T): 30/70
Substrate:  Fused Silica (Corning 7980)
Surface Flatness (P-V): λ/10
Surface Quality: 20-10
Thickness (mm): 3.00
Thickness Tolerance (mm): ±0.20
Type: Standard Beamsplitter
Wavelength Range (nm): 400 - 700
Wedge Angle: 30 arcmin

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant