

## 25mm Diameter, 75R/25T, Plate Beamsplitter



Stock #46-608 10 TO 12 DAYS

-

1

+

₹4,611.00

ADD TO CART

|                               |
|-------------------------------|
| Qty 1-9                       |
| ₹4,611.00                     |
| Qty 10+                       |
| ₹3,480.00                     |
| Volume Pricing                |
| <a href="#">Request Quote</a> |

Get Product Downloads



**Coating Specification:**  
Surface 1: Dielectric, ±5% R/T @ 550nm  
Surface 2: Uncoated

**Construction:**  
Plate

**Diameter (mm):**  
25.00

|                                                           |
|-----------------------------------------------------------|
| <b>Dimensional Tolerance (mm):</b><br>±0.38               |
| <b>Edges:</b><br>Cut                                      |
| <b>Reflection/Transmission Ratio (R/T):</b><br>75/25      |
| <b>Substrate:</b> <input type="checkbox"/><br>Float Glass |
| <b>Surface Flatness (P-V):</b><br>4 - 6λ                  |
| <b>Surface Quality:</b><br>80-50                          |
| <b>Thickness (mm):</b><br>1.00                            |
| <b>Type:</b><br>Standard Beamsplitter                     |
| <b>Wavelength Range (nm):</b><br>400 - 700                |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
| <b>Reach 240:</b><br><a href="#">Compliant</a>             |