

TECHSPEC®

25mm Diameter x 150mm FL Uncoated, UV PCX Cylinder Lens



Stock #68-175 CLEARANCE 10 TO 12 DAYS

-

1

+

₹9,566.00

ADD TO CART

Qty 1+
₹9,566.00

Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
25.00 +0.0/-0.2

Effective Focal Length EFL (mm):
150.00

Substrate: ☐
[Fused Silica](#) (Coming 7980)

f#:
6.00

Numerical Aperture NA:
0.08

Coating:	Uncoated
Type:	Cylinder Lens, Plano-Convex
Wavelength Range (nm):	200 - 2200
Back Focal Length BFL (mm):	147.94
Center Thickness CT (mm):	3.00
Center Thickness Tolerance (mm):	±0.1
Edge Thickness ET (mm):	1.85
Focal Length Tolerance (%):	±3
Radius R (mm):	68.77
Surface Quality:	40-20
Wedge Tolerance (arcmin):	15.00

Regulatory Compliance

RoHS:	Compliant
Certificate of Conformance:	View