

TECHSPEC®

25mm Diameter x 250mm FL, Uncoated, Laser Grade PCX Lens



TECHSPEC Laser Grade PCX Lenses

Stock **#67-099** 10 TO 12 DAYS
[Other Coating Options](#)

-

1

+

₹15,747.00

ADD TO CART

Qty 1-5

₹15,747.00

Qty 6+

₹12,528.00

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
25.00 +0.00/-0.10

Effective Focal Length EFL (mm):
250.00 @ 587.6nm

Back Focal Length BFL (mm):
248.14

Coating: Uncoated
Substrate: Fused Silica (Corning 7980)
Surface Quality: 20-10
Power (P-V) @ 632.8nm: λ
Irregularity (P-V) @ 632.8nm: $\lambda/10$
Focal Length Tolerance (%): ± 1
Centering (arcmin): <1
Center Thickness CT (mm): 2.71 $\pm$ 0.10
Edge Thickness ET (mm): 2.03
Radius R₁ (mm): 114.61
Clear Aperture CA (mm): 22.5
f#: 10.00
Numerical Aperture NA: 0.05
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 200 - 2200

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View