

[See all 35 Products in Family](#)

**TECHSPEC® 25mm Diameter x 30mm FL, NIR Coated, K22R Plastic Aspheric Lens**



TECHSPEC® Plastic Aspheric Lenses

Stock #21-219 **15 In Stock**

[Other Coating Options](#)

- 1 + MRP ₹7,366

● Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1-24	₹7,366 each
Qty 25-99	₹5,246 each
Qty 100-249	₹3,834 each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

Aspheric Lens **Type:**

**Physical & Mechanical Properties**

25.00 ±0.15 **Diameter (mm):**

<5 (by design)	<b>Centering (arcmin):</b>
21.5	<b>Clear Aperture CA (mm):</b>
1.39	<b>Edge Thickness ET (mm):</b>
6.54	<b>Center Thickness CT (mm):</b>
Protective as needed	<b>Bevel:</b>
Convex	<b>Shape of Back Surface:</b>

## Optical Properties

30.00 @ 587.6nm	<b>Effective Focal Length EFL (mm):</b>
0.42	<b>Numerical Aperture NA:</b>
26.04	<b>Back Focal Length BFL (mm):</b>
Zeonex K22R	<b>Substrate:</b> <input type="checkbox"/>
587.6	<b>Aspheric Design Wavelength (nm):</b>
BBAR (600-1000nm)	<b>Coating:</b>
R <sub>avg</sub> <0.7% @ 600 - 1000nm	<b>Coating Specification:</b>
80-50	<b>Surface Quality:</b>
1.2	<b>f#:</b>
188	<b>Radius R<sub>2</sub> (mm):</b>
600 - 1000	<b>Wavelength Range (nm):</b>
Infinite	<b>Conjugate Distance:</b>
587.60	<b>Focal Length Specification Wavelength (nm):</b>

## Environmental & Durability Factors

-30 to 70	<b>Operating Temperature (°C):</b>
-----------	------------------------------------

## Regulatory Compliance

<a href="#">Compliant</a>	<b>RoHS 2015:</b>
<a href="#">View</a>	<b>Certificate of Conformance:</b>
<a href="#">Compliant</a>	<b>Reach 250:</b>
United States	<b>Country of Origin:</b>
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	<b>Imported By:</b>

## Product Details

- Full Prescription Data Available
  - Standard 25mm Diameter for Easy System Integration
  - High Numerical Aperture Designs for Superior Light Collection
- TECHSPEC® Plastic Aspheric Lenses offer a lightweight alternative to glass spherical or aspherical lenses. Designed with a standard 25mm diameter, these lenses can be easily integrated into most systems and applications using standard mounting hardware. The plastic substrate provides exceptional value while still maintaining excellent performance and a high numerical aperture. TECHSPEC® Plastic Aspheric Lenses feature low haze, low autofluorescence, and excellent coating adhesion, making these lenses ideal for OEM and research applications alike. For alternate designs or custom coating requirements, please contact our [Sales Department](#).

## Technical Information



;