

TECHSPEC® 25mm H x 50mm L x 100mm FL Uncoated, Illumination Grade PCX Cylinder Lens



Stock **#46-023** [CONTACT US](#)

-

1

+

₹9,570.00

ADD TO CART

Qty 1-5
₹9,570.00
Qty 6+
₹7,656.00
Volume Pricing
Request Quote

Get Product Downloads



Effective Focal Length EFL (mm): 100.00
Substrate: N-BK7
f/#: 4
Numerical Aperture NA:

0.13
Coating: Uncoated
Type: Cylinder Lens, Plano-Convex
Wavelength Range (nm): 350 - 2200
Back Focal Length BFL (mm): 97.98
Center Thickness CT (mm): 3.16
Center Thickness Tolerance (mm): ±0.1
Dimensional Tolerance (mm): +0.0/-0.2
Dimensions (mm): 25.0 x 50.0
Edge Thickness ET (mm): 1.63
Focal Length Tolerance (%): ±3
Radius R₁ (mm): 51.85
Surface Quality: 60-40

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View