

**TECHSPEC® 25mm, MgF<sub>2</sub> Coated , Penta Prism**



Stock **#42-779** **20+ In Stock**

MRP ₹14,326

**i** Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1-5	₹14,326 each
Qty 6-25	₹11,501 each
Qty 26-49	₹10,694 each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

Penta Prism **Type:**

**Physical & Mechanical Properties**

25.00 **Length (mm):**

±0.10 **Dimensional Tolerance (mm):**

Protective as needed	<b>Bevel:</b>
25.00	<b>Length of Legs (mm):</b>
<b>Optical Properties</b>	
MgF <sub>2</sub> & Aluminized	<b>Coating:</b>
<b>N-BK7</b>	<b>Substrate:</b> <input type="checkbox"/>
60-40	<b>Surface Quality:</b>
Right-Handed	<b>Image Orientation:</b>
<b>Coating Specification:</b> Entrance/Exit Faces: R <sub>avg</sub> ≤ 1.75% @ 400 - 700nm Reflecting Surfaces: Aluminized, Inconel & Black Paint	
90	<b>Ray Deviation (°):</b>
400 - 700	<b>Wavelength Range (nm):</b>
<b>Damage Threshold, By Design:</b> <input type="checkbox"/> Entrance & Exit Faces: 10 J/cm <sup>2</sup> @ 532nm, 10ns Reflecting Surfaces: 0.3 J/cm <sup>2</sup> @ 532 & 1064nm, 10ns	
±5	<b>Beam Deviation Tolerance (arcmin):</b>
1.00	<b>Power (fringes) @ 632.8nm:</b>
0.25	<b>Irregularity (fringes) @ 632.8nm:</b>
<b>Regulatory Compliance</b>	
<b>Compliant</b>	<b>RoHS 2015:</b>
<b>Compliant</b>	<b>Reach 223:</b>
<b>View</b>	<b>Certificate of Conformance:</b>
Singapore	<b>Country of Origin:</b>
<b>Imported By:</b> Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	

## Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

## Product Details


- Ray Deviation of 90°
- Right Handed Image
- Optical Tool for Defining a Right Angle
- Additional [Penta Prism](#) Options Available

TECHSPEC® N-BK7 Penta Prisms are five-sided prisms featuring a ray deviation of 90° and a right-handed image. The reflecting surfaces are aluminized. Slight movement of the prism does not affect the true right angle at which light rays are reflected, making a penta prism the ideal optical tool for defining a right angle in an optical system. TECHSPEC® N-BK7 Penta Prisms are made from precision N-BK7 for use in a variety of visible light applications. These prisms are offered with a VIS 0° or MgF<sub>2</sub> coating, in a variety of sizes.

## Technical Information



Penta Prism Ray Path



Penta Prism Tunnel Diagram

Stock No.	Coating	Dimensions	
		A	B
#85-159	MS 0°	0.50	0.60
#85-160	MS 0°	1.00	1.20
#45-112	MgF <sub>2</sub>	5.00	6.10
#48-595	MS 0°		
#32-030	MgF <sub>2</sub>	10.00	11.95
#48-596	MS 0°		
#43-502	MgF <sub>2</sub>	15.00	15.96
#48-597	MS 0°		
#31-051	MgF <sub>2</sub>	20.00	21.65
#48-598	MS 0°		
#42-779	MgF <sub>2</sub>	25.00	27.90
#47-458	MgF <sub>2</sub>		
#48-599	MS 0°		
#45-073	MgF <sub>2</sub>	30.00	32.47
#48-600	MS 0°		
#45-402	MgF <sub>2</sub>	35.00	37.88
#48-601	MS 0°		
#45-674	MgF <sub>2</sub>	40.00	43.30
#48-602	MS 0°		
#45-675	MgF <sub>2</sub>	45.00	48.71
#48-603	MS 0°		
#45-676	MgF <sub>2</sub>	50.00	54.12
#47-459	MgF <sub>2</sub>		
#48-604	MS 0°		

