

TECHSPEC[®] 25mm N-SF11 Uncoated Equilateral Prism



Equilateral Prisms

Stock **#47-277** 20+ In Stock

-

1

+

₹13,050

ADD TO CART

Volume Pricing	
Qty 1-5	₹13,050 each
Qty 6-25	₹11,700 each
Qty 26-49	₹10,440 each
Need More?	Request Quote

Product Downloads

General	
Equilateral Prism	Type:
Physical & Mechanical Properties	
25.00	Length of Face (mm):
25.00	Length (mm):

±0.1		Dimensional Tolerance (mm):
Optical Properties		
Uncoated	Coating:	
N-SF11	Substrate: ☐	
40-20	Surface Quality:	
±2	Angle Tolerance (arcmin):	
Dispersion	Image Orientation:	
400 - 2500	Wavelength Range (nm):	
2.50	Power (fringes) @ 632.8nm:	
0.50	Irregularity (fringes) @ 632.8nm:	
Regulatory Compliance		
View	Certificate of Conformance:	
Singapore	Country of Origin:	
Edmund Optics India Private Limited	Imported By:	

Product Details

- Ideal for Light Dispersion
- Sizes Ranging from 5 - 50mm
- Available Uncoated or Anti-Reflection Coated
- Additional [Equilateral Prism](#) Options Available

TECHSPEC® Equilateral Prisms feature three equal 60° angles and are often referred to as dispersing prisms. Equilateral prisms are ideal for wavelength separating applications and light dispersion. These prisms are available in sizes ranging from 5-50mm. Our TECHSPEC® Equilateral Prisms are offered uncoated or with a single layer MgF2 anti-reflection coating. Additional [Equilateral Prism](#) options are available.

Technical Information

