

25mm Travel, 0.01mm Grad. Mic. Drive S-Face



Drive Mechanisms

Stock **#33-731** **5 In Stock**

-

1

+

₹8,700

ADD TO CART

Volume Pricing	
Qty 1+	₹8,700 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

General	
Metric	Type:
Mitutoyo	Manufacturer:

w/ Ratchet	Note:
------------	-------

Physical & Mechanical Properties	
25	Travel (mm):
0.01	Graduation (mm):
10	Stem Diameter (mm):
Plain/Spherical	Stem/Spindle:
15	Stem Length (mm):
6.35	Spindle Diameter (mm):
27	Min. Spindle Length (mm):
18	Max. Diameter (mm):
109	Overall Length (mm):
Hardware & Interface Connectivity	
Metric Micrometer	Type of Drive:
Regulatory Compliance	
Exempt	RoHS 2015:
View	Certificate of Conformance:
Contains SVHC(s)	REACH 241:

PRODUCT DETAILS

- Micrometer, Fine Screw, Digital and Differential Options Available
 - Compatible with our [Ball Bearing Stages](#)
- These drive mechanisms add versatility to our selection of [ball bearing stages](#). Four options are available: micrometer (English and Metric), fine screw, digital, and differential.
- Please reference individual product descriptions to see which stages are compatible with each drive mechanism.

TECHNICAL INFORMATION

