

TECHSPEC[®] 25mm VIS, 30R/70T, Non-Polarizing Cube Beamsplitter



Stock #13-420 10 TO 12 DAYS

-

1

+

₹22,446.00

ADD TO CART

Qty 1-5
₹22,446.00
Qty 6+
₹17,574.00
Volume Pricing
Request Quote

Get Product Downloads



Beam Deviation (arcmin):
≤2

Bevel:
Protective bevel as needed

Clear Aperture (%):
>90

Coating:

MS
Coating Specification: R_{avg} <0.5% @ 430 - 670nm
Construction: Cube
Dimensions (mm): 25.0 x 25.0 x 25.0 ±0.1
Reflection/Transmission Ratio (R/T): 30/70
Substrate:  N-BK7
Surface Flatness (P-V): λ/8
Surface Quality: 40-20
Type: Non-Polarizing Beamsplitter
Wavelength Range (nm): 430 - 670
[Ts-Tp]: <6%
Absolute Transmission (%): 65 ±10
Average Transmission (%): 65 ±5

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View